


SW20-GSH-145-SH

Machine: STAR MICRONICS

Type: SW20

Emplacement, N°: Coulisse linéaire / T600

Travail sur: Broche principale


Type de travail:  $n_{\max}$: - [rpm] $i (n_i / n_o)$: 1 / 1

Attachement: Arbre Ø3.5/4.5mm

Sans refroidissement

Infos: Tête de taillage interchangeable (GSH-145-SH, +15°/-3°) montée sur queue STAR2-PCR.

SW20-GSH-145-SH



Machine: STAR MICRONICS

Type: SW20

Location, N°: Gangtool / T600

Work on: Main spindle

Type of work:




n_{max} : - [rpm]

$i (n_i / n_o)$: 1 / 1

Attachement: Shaft Ø3.5/4.5mm

Without coolant

Infos: Interchangeable hobbing head (GSH-145-SH, +15°/-3°) mounted on shank STAR2-PCR.

SW20-GSH-145-SH

Machine: STAR MICRONICS

Typ: SW20

Position, N°: Vertikalhalter / T600

Arbeit über: Hauptspindel


Arbeitstyp:

 $n_{\max}$: - [rpm] $i (n_i / n_o)$: 1 / 1

Befestigung: Schaft Ø3.5/4.5mm

Ohne Kühlmittel

Infos: Austauschbar Abwälzfräserhalter (GSH-145-SH, +15°/-3°) auf Schaft STAR2-PCR fixiert.

SW20-GSH-145-SH

Macchina: STAR MICRONICS

Tipo: SW20

Posizione, N°: Slitta lineare / T600

Lavoro al: Mandrino principale

Tipo di lavoro:

 $n_{\max}$: - [rpm] $i (n_i / n_o)$: 1 / 1

Ataccamento: Codolo Ø3.5/4.5mm

Senza refrigerante

Informazioni: Testa a tagliare intercambiabile (GSH-145-SH, +15°/-3°) salita sulla coda STAR2-PCR.